

MAXX Indur2

5L O

4 028159 034154

ECOLAE

* 1

MAXX Indur2 🥌

10

DE/020/26

MAXX Indur2 SUPER WETTING HARD FLOOR MAINTAINANCE CLEANER

Performance

- Thoroughly cleans surfaces from traffic dirt and reduces dirt adhesion with regular use
- High dirt absorbing capability and low foaming
- Includes water soluble polymers to leave a non-build-up, dirtrepellent film on the floor that will be renewed by next cleaning

Efficiency


- ▲ Effective in low concentration (from 0,25%) to reduce cleaning costs
- Increase intervals between maintenance cleaning and lowering maintenance costs
- Used in spray buffing method, it removes scuff marks, repairs floor finish and restores initial gloss

Safety

- Material friendly formulation allows use on most water resistant hard floors
- Colour-coded system to ensure the use of the right product for the right cleaning task

Certified according to DIN 18032*

/



Super Wetting Technology

MAXX Indur2 has a super wetting capability and is well suited for highly water repellent or porous surfaces.

Recommended Customer Areas

 Daily office cleaning, public buildings, hospitals, schools, etc.

Use Instruction:

FLOOR CLEANING METHOD:








4

- 1. Check hygiene plan for detailed use information.
- 2. Dilute 25 50 ml of MAXX Indur2 in 10 L water depending on the level of soiling.
- 3. Wipe the floor with microfibre mop.
- 4. No rinsing required.

SPRAY BUFFING METHOD:



- 1. Check hygiene plan for detailed use information.
- 2. Dilute 25 50 ml of MAXX Indur2 in 500 ml water into a MAXX Indur2 refill bottle or directly in the spray system of the machine.
- 3. Spray on the floor over approximately 2 m² at a time and polish with a high-speed single disc machine with an appropriate pad until clean and dry.

SPECIAL NOTES / INFORMATION:

Only a small quantity of the product is needed compared to normal products. Proper dosage saves costs and minimizes environmental impact.

Test material compatibility in a small inconspicuous area before use. Position warning signs 'Attention wet floor' and leave in place until surface is totally dry.

Suitable for use on all emulsion floor finishes and hydrophobic surfaces (e.g. polyurethane).

Miscability Certificates available for selected Ecolab disinfection products.

For professional use only!

Safety Data Sheet for professional users available on request. Do not mix with any other product. Keep out of reach of children.


Worldwide Headquarters Ecolab Inc. 370 Wabasha Street N St. Paul, MN 55102

European Headquarters Ecolab Europe GmbH Richtistr. 7 CH-8304 Wallisellen

STORAGE CONDITIONS:

Recommended storage temperature between 0 °C and 40 °C.

pH value (100%)



PRODUCT	ARTICLE No.	PACK SIZE
MAXX Indur2	9084420	12 x 1L Bottle
MAXX Indur2	9084440	2 x 5L Bottle

Wetting with 'classic' cleaning products

Super wetting effect

www.ecolab.com

© 2015 Ecolab USA Inc. All rights reserved